

ACRILNAR 240 LN

INFORMATIVE DATA SHEET



ACRILNAR

COMPOSITION

BACKING: biaxially oriented polypropylene film ADHESIVE: water based acrylic polymers dispersion CORE: recycled paper and paperboard

SUITABLE FOR

Hand dispensers and automatic sealing machines; sealing of recycled cardboard boxes

AVAILABLE COLOURS

Brown - white - transparent

Excellent resistance at low temperature after application. The characteristics of the adhesive make it particularly resistant to ageing caused by light sources, while maintaining its functionality for a long time.

ACRILNAR products are also available in a food contact approved version: contact us for further information.



BACKING THICKNESS 28 μm



BREAKING LOAD > 39 N/cm



LOW NOISE UNWINDING (on request)



LIGHT WEIGHT PACKAGING

ORGANIC SOLVENTS FREE

SUITABLE FOR LOW TEMPERATURES PACKAGING

*

NAR S.P.A. Legnaro (PADOVA) ITALY www.nar-spa.com









INFORMATIVE DATA SHEET



| | | | \sim | iii. | | | | | |
|--------------------|----------------------------|--------------------------|------------------|--------------------------|-----------------------------|---|------------------------------|-------------------------------|------------------------------|
| | backing thickness µm | total thickness µm | adhesion N/cm | breaking load N/cm | elongation at break % | available colours | heavy weight packaging | medium weight packaging | light weight packaging |
| ACRILNAR 220 | 25 | 39 | > 2,0 | > 36 | > 116 | • Ø | | | • |
| ACRILNAR 230 | 25 | 41 | > 2,2 | > 36 | > 116 | | | | • |
| ACRILNAR 230 LN | 25 | 43 | > 2,6 | > 36 | > 116 | | | | • |
| ACRILNAR 240 | 28 | 44 | > 2,2 | > 39 | > 116 | | | | • |
| ACRILNAR 240 LN | 28 | 46 | > 2,6 | > 39 | > 116 | | | | • |
| ACRILNAR 240 NN | 28 | 49 | > 2,9 | > 39 | > 116 | | | | • |
| ACRILNAR 260 | 32 | 48 | > 2,2 | > 45 | > 116 | | | • | |
| ACRILNAR 260 LN | 32 | 50 | > 2,6 | > 45 | > 116 | | | • | |
| ACRILNAR 260 NN | 32 | 53 | > 2,9 | > 45 | > 116 | | | • | |
| ACRILNAR 260 NN HT | 32 | 55 | > 3,1 | > 45 | > 116 | | | • | |
| ACRILNAR 265 NN | 32 | 53 | > 2,9 | > 45 | > 116 | $\bullet \bullet \bullet \bullet \bullet \bullet \bullet$ | | • | |
| ACRILNAR 265 HT | 32 | 55 | > 3,1 | > 45 | > 116 | $\bullet \bullet \bullet \bullet \bullet \bullet \bullet \bullet$ | | • | |
| ACRILNAR 270 NN | 35 | 56 | > 2,9 | > 47 | > 116 | | | • | |
| ACRILNAR 270 NN HT | 35 | 58 | > 3,1 | > 47 | > 116 | | | • | |
| ACRILNAR 276 NN | 35 | 62 | > 3,4 | > 47 | > 116 | | • | | |
| ACRILNAR 280 NN | 40 | 65 | > 3,1 | > 54 | > 116 | | • | | |
| ACRILNAR 290 NN | 50 | 75 | > 3,1 | > 58 | > 116 | | • | | |

brown

⊘ transparent

○ white

🛑 orange

red

black

yellow

light blue

• green

blue



NAR S.P.A. Legnaro (PADOVA) ITALY www.nar-spa.com

It is good practice to use the product within 12 months from purchase date (6 months if jumbo roll). The rolls must be kept in their original packing. Keep the product out of the light and protect from direct heat sources. The tape must be kept in a dry place, at humidity level below 65%, preferably at a temperature between 15° C and 25° C. If the storage temperature is different, restore the tape back to above level before using it. The values in the informative data sheets are the average results of tests made on our standard production and are not legally binding. The aesthetic and technical features may be subject to some changes caused by ageing, even though the quality level of the product is maintained. Nar shall not be liable for direct damages or for any consequence arising from the misuse of the product. We suggest the verification of the product witability to the specific condition of use. Additional indications are available in the last edition of the booklet "Recommendation regarding choice, storing and use of pressure sensitive tapes" published by Federazione Gomma Plastica.



www.nar-spa.com/ technical-notes.html