



ACRILNAR 260 NN HT

INFORMATIVE DATA SHEET

H TACK

*

HIGH ADHESIVE MASS

MEDIUM WEIGHT PACKAGING

SUITABLE FOR LOW TEMPERATURES PACKAGING

ORGANIC SOLVENTS FREE

ACRILNAR

COMPOSITION

BACKING: biaxially oriented polypropylene film ADHESIVE: water based acrylic polymers dispersion CORE: recycled paper and paperboard

SUITABLE FOR

Hand dispensers; sealing of recycled cardboard boxes; flexographic printing process

AVAILABLE COLOURS

Brown - white - transparent

Excellent resistance at low temperature after the application. High adhesive mass. The characteristics of the adhesive make it particularly resistant to ageing caused by light sources, while maintaining its functionality for a long time. Suitable for flexographic print. ACRILNAR products are also available in a food contact approved version: contact us for further information.



BACKING THICKNESS 32 μm



ADHESION > 3,1 N/cm



SUITABLE FOR FLEXOGRAPHIC PRINT



NAR S.P.A. Legnaro (PADOVA) ITALY www.nar-spa.com











INFORMATIVE DATA SHEET



			\sim	iii.					
	backing thickness µm	total thickness µm	adhesion N/cm	breaking load N/cm	elongation at break %	available colours	heavy weight packaging	medium weight packaging	light weight packaging
ACRILNAR 220	25	39	> 2,0	> 36	> 116	• Ø			•
ACRILNAR 230	25	41	> 2,2	> 36	> 116				•
ACRILNAR 230 LN	25	43	> 2,6	> 36	> 116				•
ACRILNAR 240	28	44	> 2,2	> 39	> 116				•
ACRILNAR 240 LN	28	46	> 2,6	> 39	> 116				•
ACRILNAR 240 NN	28	49	> 2,9	> 39	> 116				•
ACRILNAR 260	32	48	> 2,2	> 45	> 116			•	
ACRILNAR 260 LN	32	50	> 2,6	> 45	> 116			•	
ACRILNAR 260 NN	32	53	> 2,9	> 45	> 116			•	
ACRILNAR 260 NN HT	32	55	> 3,1	> 45	> 116			•	
ACRILNAR 265 NN	32	53	> 2,9	> 45	> 116	$\bullet \bullet \bullet \bullet \bullet \bullet \bullet$		•	
ACRILNAR 265 HT	32	55	> 3,1	> 45	> 116	$\bullet \bullet \bullet \bullet \bullet \bullet \bullet \bullet$		•	
ACRILNAR 270 NN	35	56	> 2,9	> 47	> 116			•	
ACRILNAR 270 NN HT	35	58	> 3,1	> 47	> 116			•	
ACRILNAR 276 NN	35	62	> 3,4	> 47	> 116		•		
ACRILNAR 280 NN	40	65	> 3,1	> 54	> 116		•		
ACRILNAR 290 NN	50	75	> 3,1	> 58	> 116		•		

brown

⊘ transparent

○ white

🛑 orange

red

black

yellow

light blue

• green

blue



NAR S.P.A. Legnaro (PADOVA) ITALY www.nar-spa.com

It is good practice to use the product within 12 months from purchase date (6 months if jumbo roll). The rolls must be kept in their original packing. Keep the product out of the light and protect from direct heat sources. The tape must be kept in a dry place, at humidity level below 65%, preferably at a temperature between 15° C and 25° C. If the storage temperature is different, restore the tape back to above level before using it. The values in the informative data sheets are the average results of tests made on our standard production and are not legally binding. The aesthetic and technical features may be subject to some changes caused by ageing, even though the quality level of the product is maintained. Nar shall not be liable for direct damages or for any consequence arising from the misuse of the product. We suggest the verification of the product witability to the specific condition of use. Additional indications are available in the last edition of the booklet "Recommendation regarding choice, storing and use of pressure sensitive tapes" published by Federazione Gomma Plastica.



www.nar-spa.com/ technical-notes.html